


Get Started with Overo[™] Computer-on-Module

TI OMAP3503-based Overo™ Earth and Water COMs TI OMAP3530-based Overo[™] Fire and Air COMs






58mm x 17mm x 4.2mm


Dimensions:

Wi2Wi, Inc.

The device must be used at least 20cm away from a user's body.



Start with a Console Session



Using a LCD Touchscreen

To set the 'defaultdisplay' variable in U-Boot:

· Hit 'Enter' to interrupt the boot sequence

- •Type 'setenv defaultdisplay lcd43; saveenv; ' and press 'Enter'. (replace 'lcd43' with 'lcd35' for 3.5" screens)
- Type 'reset' then press 'Enter' or simply press the 'reset' button on the expansion board

Visit www.gumstix.org for the latest tools, resources, community info and help getting started.

Developer Center



Adding Peripherals